


Rhino Rack 2500 Series - DK504 instruction

CONTROLLED

CROSSBAR IDENTIFICATION







VA crossbar

EURO crossbar

HD crossbar

					FRONT CROSSBAR							REA	AR CROSSE	BAR
					(E) VA	EURO	HD				ŒĐ VA	EURO	HD	
Vehicle	Date	Crossbar	Front Right Pad/Clamp	Front Left Pad/Clamp	Measurement strip length per side		Measurement Distance (x)	Foot plate arrow direction	Rear Right Pad/Clamp	Rear Left Pad/Clamp	Measurement strip length per side		Measurement Distance (x)	Foot plate arrow direction
RAM 1500 Quad Cab	19 -	1500	M282 SUB0155	M281 SUB0155	150mm	95mm	1188mm / 46 3/4"	OUT	M284 SUB0155	M283 SUB0155	143mm	88mm	1174mm / 46 1/4"	OUT
			FORV	VARD	RD		40 0/4		FOR	WARD			40 1/4	
RAM 1500 Crew Cab	19 -	1500	M282 SUB0155 FORV	M281 SUB0155 VARD	150mm	95mm	1188mm / 46 3/4"	OUT		M283 SUB0155 WARD	143mm	88mm	1174mm / 46 1/4"	OUT





Rhino Rack 2500 Series - DK504 instruction


Measurement A: CENTRE of door jamb to CENTRE arrow of leg foot plate.


Measurement B: CENTRE of Front leg foot plate arrow to CENTRE of Rear leg foot plate arrow.

Carrying capacity: Roof rack is rated up to 75kg. Please refer to manufacturers handbook for your vehicles maximum roof load capacity. Always use the lower of the two figures.

If your vehicle is not listed on this fitting instruction please refer to your countries Rhino-Rack web site for the latest information.

Direction of Pad Arrow and Foot Plate Arrow





VEHICLE	Date	Measurement A	Measurement B	Load Rating up to (includes racks 5kg/ 11lbs)		
RAM 1500 Quad Cab	19 - on	310mm (12 3/16")	650mm (25 9/16")	75kg / 165lbs		
RAM 1500 Crew Cab	19 - on	310mm (12 3/16")	650mm (25 9/16")	75kg / 165lbs		